

LIGHTWEIGHT AND QUICK TO APPLY, THE HANDI-GRIP AND PICK-UP STICK ARE "INSTANT HANDLES" FOR GLASS LIFTING AND HANDLING.

HANDI-GRIPS

Handi-Grips reduce the chance of serious cuts and eliminate the need to lift glass by the edges. Easy to use and quick to apply, these hand-held vacuum cups are available in styles for handling flat, curved or narrow objects.

To apply a Handi-Grip, simply press it to the surface of clean glass and pump the plunger. A few quick strokes attach it securely to the glass. When the cup is properly attached and ready to lift, the plunger stays in and the red line is no longer visible.

A pair of Handi-Grip vacuum cups is ideal for lifting large glass sheets onto glass cutters, work tables, or prepared art work.

Available in low-marking rubber* for use on delicate surfaces.

(*low-marking rubber not available for the RF36HG hand cup)



LJ45HG
LP6HG
TL6HG



RF36HG

PICK-UP STICK

The Pick-Up Stick eliminates fingerprints and cut fingers when lifting glass to remove that last speck of dust before closing the back of a frame.

The Pick-Up Stick uses a small, hand-held vacuum pump to attach to smooth, nonporous surfaces such as glass and Plexiglass®. It comes with a 1-1/4" [32 mm] interchangeable rubber pad and a durable plastic handle. Optional pads are available in 3/4" [20 mm] and 1" [26 mm] diameters. To attach the Pick-Up Stick, press the pad against the glass and depress the plunger

with your thumb. Once the Pick-Up Stick is attached, the corner of the glass can be lifted without making finger smudges on the clean inside surface, allowing quick removal of annoying dust particles.

In addition to lifting corners of framing glass, the Pick-Up Stick is an indispensable tool for precise placement of stained glass, small coins, lockets and other memorabilia.



PU0950

